


Austik Fact Sheet

Thermal Transfer Labels Austik Barco Series

Pen series are designed for all types of writing instruments that use a clip. These tags may be threaded over the clip or held in place by the clip, (see the diagram below). Pen tags are for use with thermal transfer barcode printers only. As with all bar code labels, Austik tags may incorporate custom printing in the blank areas. The label Barco-PI accepts all popular bar codes including EAN13 and UPCA and E.


BARCO-PI

2,500 Labels Per Pack in Rolls | Labels Across



AusSilk®, will not tear
Adhesive Free Center Sections
Washable in Ultra-Sonics

How It Works



THREADED

For standard size clips you can thread the tag over the clip.

HELD BY CLIP

For thick clips the label may be held in place by the clip end locating in the bottom hole.

The Tags have been specifically designed for writing instruments. After printing the tags fold in half creating the finished label and double strength clear plastic tab. This also means that the tabs cannot come apart should the adhesive fail as once they are threaded both sides are held firmly in place.

Barco-PI Samples printed with Austik Sapphire-300 Printer.